



S2619

35MR16/T/NFL/C
35 watt; Halogen; MR16; 4000 Average rated Hours; Miniature
2 Pin Round base; 12 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output
- 12 volt



S2619

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S2619	046135583049	35	12	MR16	Miniature 2 Pin Round	GU5.3/GX5.3	35MR16/T/NFL/C
MOL In Inches	MOD In Inches	Filament	Kelvin Temp	Color	Average Rated Hours	Pack	Package Type
1 3/4"	2.00"	AX	2900	Warm White	4000	20	Box
Beam Spread Deg	Lens	CBCP	Dimmable/Non-Dimmable	RoHS Compliant			
25	Y	3100	Dimmable	Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

