



S2644

20ALR12/FL/FRST
20 watt; Halogen; ALR12; GBF; Frosted; 2000 Average rated Hours; DC Bay base; 12 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output
- 12 volt



S2644

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S2644	046677340032	20	12	ALR12	DC Bay	BA15d	20ALR12/FL/FRST
ANSI Code	MOL In Inches	MOD In Inches	Filament	Kelvin Temp	Color	Average Rated Hours	Pack
GBF	1 3/8"	1 1/2"	C-8	2900	Warm White	2000	50
Package Type	Beam Spread Deg	Lens	CBCP	Dimmable/Non-Dimmable	RoHS Compliant		
Box	34	Y	350	Dimmable	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

