



50MR16/GU10/FL
50 watt halogen; MR16; 2000 average rated hours; GU10 base;
120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S3502

Item Number	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage	MOL In Inches
S3502	50	MR16	GU10	GU10	50MR16/GU10/FL	120	1 7/8"
MOL in mm	Filament	Average Rated Hours	Pack	Package Type	Beam Spread	Lens	CBCP
47.63 mm	CC-8	2000	12	CD/1	FL 36	Y	1700



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

