



S3516

35MR16/GU10/FL
35 watt; Halogen; MR16; 2000 Average rated Hours; 290 Lumens; GU10 base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S3516

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S3516	045923035166	35	120	MR16	GU10	GU10	35MR16/GU10/FL
MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours	Pack
1 7/8"	2.00"	CC-8	290	2900	Warm White	2000	240/12
Package Type	Beam Spread Deg	Lens	CBCP	Dimmable/Non-Dimmable	RoHS Compliant		
Box	36	Y	400	Dimmable	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

