



S3744

25HX10 1/2
25 watt HX10.5 Incandescent; Clear; 1500 average rated hours;
175 lumens; Candelabra base; 120 volts; 2/Card

Features

- Decorative incandescent
- Long Life
- Brass Base



S3744

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3744	045923037443	25	HX10.5	Candelabra	E12	25HX10 1/2	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	4 15/16"	2.50"	C-7A	175	1500	120/12	CD/2

Dimmable/Non-Dimmable	RoHS Compliant
Dimmable	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

