



S4187

75MR16/FL/C
75 watt; Halogen; MR16; EYC; 2000 Average rated Hours;
Miniature 2 Pin Round base; 12 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output
- 12 volt

S4187

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4187	045923041877	75	12	MR16	Miniature 2 Pin Round	GU5.3/GX5.3	75MR16/FL/C

ANSI Code	MOL In Inches	MOD In Inches	Filament	Kelvin Temp	Color	Average Rated Hours	Pack
EYC	1 7/8"	2.00"	C-6	2900	Warm White	2000	240/12

Package Type	Beam Spread Deg	Lens	CBCP	Dimmable/Non-Dimmable	RoHS Compliant
Box	38	Y	1650	Dimmable	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

