



Product 54836

Number:

Order BHC/DYS/DYV

Abbreviation:

General Description: 600 watt, tungsten halogen, medium to high voltage, single-ended

Product Information

Abbrev. With Packaging Info.	BHCDYSDYV 120V 24/CS 1/SKU
ANSI Code	BHC/DYS/DYV
Application	Projector, Microfilm, Stage & Studio
Average Rated Life (hr)	75
Base	GZ9.5 Bip in Prefocus
Bulb	T6
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature (K)	3200
Diameter d (in)	0.787
Diameter d (mm)	20.00
Distance a (in)	1.424
Distance a (mm)	36.5
Filament	CC-6
Filament Dimensions Length (in)	0.187
Filament Dimensions Length (mm)	4.8
Filament Dimensions Width (in)	0.441
Filament Dimensions Width (mm)	11.3
Lamp Finish	Clear
Length l (in)	2.496
Length l (mm)	64
Length l max. (in)	2.496
Length l max. (mm)	64
LIF Code	A1/264
Light Center Length - LCL (in)	1.424
Light Center Length - LCL (mm)	36.5
Luminous Flux (lm)	17500
Maximum Overall Length - MOL (in)	2.496
Maximum Overall Length - MOL (mm)	64
Nominal Voltage (V)	120.00
Nominal Wattage (W)	600.00
Operating Position	s 90

Type of Current

AC

Footnotes

- s (Operating Position) = Vertical, base down