



Product Number: 54840

Order Abbreviation: ELC

General Description: 250 watt, tungsten halogen, low to medium voltage with reflector

Product Information

| | |
|-----------------------------------|---|
| Abbrev. With Packaging Info. | ELC 24V 24/CS 1/SKU |
| Application | Overhead projection, fiber-optic, entertainment |
| Average Rated Life (hr) | 50 |
| Base | GX5.3 Bipin |
| Bulb | MR16 |
| Class | C (gas) |
| Color Rendering Index (CRI) | 100 |
| Color Temperature (K) | 3400 |
| Diameter d (in) | 39.366 |
| Diameter d (mm) | 999.90 |
| Filament | C8 |
| Lamp Finish | Clear |
| Length l (in) | 1.765 |
| Length l (mm) | 44.83 |
| Length l max. (in) | 1.765 |
| Length l max. (mm) | 44.83 |
| LIF Code | A1/259 |
| Luminous Flux (lm) | 800 |
| Maximum Overall Length - MOL (in) | 1.765 |
| Maximum Overall Length - MOL (mm) | 44.83 |
| Nominal Voltage (V) | 24.00 |
| Nominal Wattage (W) | 250.00 |
| Operating Position | Any |
| Reflector Coating | WHITE |
| Type of Current | AC |
| Working Distance a (in) | 1.238 |
| Working Distance a (mm) | 31.75 |

Footnotes

- Lumens refers to screen lumens.