



**Product** 54979

**Number:**

**Order** FHS

**Abbreviation:**

**General** 300 watt, tungsten halogen, low to medium voltage with reflector

**Description:**

### Product Information

Abbrev. With Packaging Info.	FHS 82V 24/CS 1/SKU
ANSI Code	FHS
Application	Projector - Slide
Average Rated Life (hr)	70
Base	GX5.3 Bipin
Bulb	T3.5
Class	C (gas)
Color Rendering Index (CRI)	100
Diameter d (in)	1.654
Diameter d (mm)	42.00
Filament	CC-8
Lamp Finish	Clear
Length l (in)	1.755
Length l (mm)	45
Length l max. (in)	1.755
Length l max. (mm)	45
Luminous Flux (lm)	650
Maximum Overall Length - MOL (in)	1.755
Maximum Overall Length - MOL (mm)	45
Nominal Voltage (V)	82.00
Nominal Wattage (W)	300.00
Operating Position	s 90
Reflector Coating	42.00
Type of Current	AC
Working Distance a (in)	5.948
Working Distance a (mm)	152.5

### Footnotes

- s (Operating Position) = Vertical, base down
- Lumens refers to screen lumens.