

Product 54448**Number:****Order** EYB-5**Abbreviation:****General** 360 watt, tungsten halogen, low voltage without reflector**Description:****Product Information**

Abbrev. With Packaging Info.	EYB5 85.5V 24/CS 1/SKU
ANSI Code	EYB-5
Application	Projector, Microfilm, Stage & Studio
Average Rated Life (hr)	75
Base	G5.3 Bip in
Bulb	T3.5
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature (K)	3250
Diameter d (in)	0.441
Diameter d (mm)	11.20
Distance a (in)	1.240
Distance a (mm)	31.8
Filament	CC-8
Filament Dimensions Length (in)	0.300
Filament Dimensions Length (mm)	7.7
Filament Dimensions Width (in)	0.238
Filament Dimensions Width (mm)	6.1
Lamp Finish	Clear
Length l (in)	2.231
Length l (mm)	57.2
Light Center Length - LCL (in)	1.240
Light Center Length - LCL (mm)	31.8
Luminous Flux (lm)	10000
Maximum Overall Length - MOL (in)	2.231
Maximum Overall Length - MOL (mm)	57.2
Nominal Voltage (V)	85.50
Nominal Wattage (W)	360.00
Operating Position	s 90
Type of Current	AC

Footnotes

- s (Operating Position) = Vertical, base down