



BBA

120V 250W Inside Frosted A-21 E26 Base

| Specifications | |
|-------------------------|--------------------|
| Item | BBA |
| Bar Code | 00040 |
| Volts | 120 |
| Watts | 250 |
| Lumens | 8500 |
| Filament | C-9 |
| Coating | Inside Frosted |
| MOL in/mm | 4.77/121.2 |
| MOD in/mm | 2.68/68.0 |
| Avg Life | 3 |
| Bulb | A-21 |
| Base | Medium Screw (E26) |
| Watts Amps | 250 |
| CT deg K | 3400 |
| Type Use | Photoflood |
| Photo No | 277 |
| Poss Sub | BBA-LN |
| Burning Position | Any |