



S9604

5.5A19/OMNI/300/LED/50K
5.5 watt; A19 LED; 5000K; Medium base; 300° beam spread;
120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- Approved for enclosed fixtures



S9604

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9604	045923096044	120	5.5	40W	0.82	A19	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E26	5.5A19/OMNI/300/LED/50K	Dimmable	Frosted	4 1/2"	2.38"	510	25000

Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
5000	Natural Light	80	300	24	Box	ENERGY STAR	Yes

UL or ETL Listed	UL Classification	Warranty
Yes	cULus - Damp Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

