



S2420

40T9/GOLD/9S/E12/120V /Vintage
40 watt T9 Incandescent; Clear Gold; 3000 average rated hours; 160 lumens; Candelabra base; 120 volts

Features

- Vintage Style incandescent
- Historic restoration quality
- Classic, warm glow



S2420

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S2420	045923024207	40	T9	Candelabra	E12	40T9/GOLD/9S/E12/120V /Vintage	120
Color	Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack
Gold	Clear	3-1/2"	1.09"	Cage Style	160	3000	50/10
Package Type	Dimmable/Non-Dimmable		RoHS Compliant				
Box	Dimmable		Yes				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

