



S7336

40T4/50
40 watt; Hi-Pro Spiral Compact Fluorescent; 5000K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7336

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S7336	Hi-Pro	045923073366	120	40	150W	T4	Medium
ANSI Base	Lamp Code	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
E26	40T4/50	7.28"	2.63"	2600	10000	5000	Natural Light
Pack	Package Type	CRI	Hg Content	RoHS Compliant	UL or ETL Listed	Warranty	
48/12	Box	82	3.2 mg	Yes	Yes	2 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

