



S9386

4.5PAR16/LED/40'/3000K/120V
4.5 watt PAR16 LED; 3000K; 40' beam spread; Medium base;
120 volts

Features

- Direct replacement for 45W
- Halogen PAR16 lamps
- Dimmable
- Damp location
- Approved for enclosed fixtures
- Long life - 25,000 hours
- High efficiency / environmentally friendly
- No UV or IR radiation
- 3 year warranty



S9386

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9386	045923093869	120	4.5	45W	0.94	PAR16	Medium

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
E26	4.5PAR16/LED/40'/3000K/120V	Dimmable	2 7/8"	2.00"	370	25000	3000

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	Warranty
Warm White	80	40	48	Box	Yes	Yes	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

