



S9550

1.6MR11/LED/40°/3000K/12V/D
1.6 watt; LED MR11 LED; 3000K; 40° beam spread; G4 base;
12 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen MR11 lamps.



S9550

[Compatible dimmers for S9550](#)

Item Number	UPC	Voltage	Watts	Lamp Shape	Base	Lamp Code	Dimmable/Non-Dimmable
S9550	045923095504	12	1.6	MR11	GU4	1.6MR11/LED/40°/3000K/12V/D	Dimmable
MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg
1-9/16"	1-1/2"	200	25000	3000	Warm White	80	40
RoHS Compliant	UL or ETL Listed	UL Classification	Warranty				
Yes	Yes	cETLus - Damp Location Rated	3 Year Limited				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

