



# S9586

4.5CTA/AMB/LED/E26/22K/120V  
 4.5 watt Torpedo CTA LED; Amber; Candelabra base; 2200K;  
 300 lumens; 120 volts

### Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

### Compatible Dimmers

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

† When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9586

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9586	045923095863	120	4.5	40W	C11	Candelabra	E12

  

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
4.5CTA/AMB/LED/E26/22K/120V	Dimmable	Transparent Amber	4 5/16"	1.38"	300	15000	2200

  

Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
360	-20°C (-4°F) to a maximum of +45°C (113°F)	24/6	Box	Yes	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

