



# S9817

15.5A21/LED/4000K/1600L/120V/D  
 15.5 watt; A21 LED; Frosted; 4000K; Medium base; 220' beam spread; 120 volts

### Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures



S9817

[Compatible dimmers for S9817](#)

Item Number	UPC	Voltage	Watts	Power Factor	Lamp Shape	Base	ANSI Base
S9817	045923098178	120	15.5	0.96	A21	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15.5A21/LED/4000K/1600L/120V/D	Dimmable	Frosted	5-9/16"	2-5/8"	1600	25000	4000
Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Cool White	80	220	24/6	Box	ENERGY STAR	Yes	Yes
UL Classification						Warranty	
cULus - Damp Location Rated						<a href="#">3 Year Limited</a>	