



S9922

3.5W CTC/LED/27K/CL/120V
 3.5 watt C11 LED; Clear; Candelabra base; 2700K; 350 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9922

[Compatible dimmers for S9922](#)

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|--------------------------|-----------------------|-----------------------------|---|-------------------------|----------------|--------------------------------|----------------|
| S9922 | 045923099229 | 120 | 3.5 | 40W | C11 | Candelabra | E12 |
| Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
| 3.5W CTC/LED/27K/CL/120V | Dimmable | Clear | 3 7/8" | 1-3/8" | 350 | 15000 | 2700 |
| Color | CRI | Beam Spread Deg | Operating Temperature | Pack | Package Type | RoHS Compliant | Fixture Type |
| Warm White | 80 | 360 | -20C (-4F) to a maximum of +45C (+113F) | 24/6 | Box | Yes | Enclosed Rated |
| UL or ETL Listed | | UL Classification | | | | Warranty | |
| Yes | | cULus - Damp Location Rated | | | | 3 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

