

# PowerPact® Q-Frame Molded Case Circuit Breakers and Switches Catalog Numbering System

<sup>3</sup> This rating is not UL or CSA approved

**Table 2: PowerPact® Q-frame Circuit Breaker Catalog Numbers**

Ampere Rating	Fixed AC Magnetic Trip		B Interrupting 10 kA		D Interrupting 25 kA		G Interrupting 65 kA		J Interrupting 100 kA <sup>1</sup>	
	Hold	Trip	Unit-Mount	I-Line®	Unit-Mount	I-Line®	Unit-Mount	I-Line®	Unit-Mount	I-Line®
<b>2P, 240 Vac</b>										
70 A	1000 A	1800 A	QBL22070	QBA22070	QDL22070	QDA22070	QGL22070	QGA22070	QJL22070	QJA22070
80 A	1000 A	1800 A	QBL22080	QBA22080	QDL22080	QDA22080	QGL22080	QGA22080	QJL22080	QJA22080
90 A	1000 A	1800 A	QBL22090	QBA22090	QDL22090	QDA22090	QGL22090	QGA22090	QJL22090	QJA22090
100 A	1200 A	2400 A	QBL22100	QBA22100	QDL22100	QDA22100	QGL22100	QGA22100	QJL22100	QJA22100
110 A	1200 A	2400 A	QBL22110	QBA22110	QDL22110	QDA22110	QGL22110	QGA22110	QJL22110	QJA22110
125 A	1200 A	2400 A	QBL22125	QBA22125	QDL22125	QDA22125	QGL22125	QGA22125	QJL22125	QJA22125
150 A	1200 A	2400 A	QBL22150	QBA22150	QDL22150	QDA22150	QGL22150	QGA22150	QJL22150	QJA22150
175 A	1200 A	2400 A	QBL22175	QBA22175	QDL22175	QDA22175	QGL22175	QGA22175	QJL22175	QJA22175
200 A	1200 A	2400 A	QBL22200	QBA22200	QDL22200	QDA22200	QGL22200	QGA22200	QJL22200	QJA22200
225 A	1200 A	2400 A	QBL22225	QBA22225	QDL22225	QDA22225	QGL22225	QGA22225	QJL22225	QJA22225
250 A <sup>2</sup>	1200 A	2400 A	QBL22250	—	QDL22250	—	QGL22250	—	QJL22250	—
<b>3P<sup>3</sup>, 240 Vac</b>										
70 A	1000 A	1800 A	QBL32070	QBA32070	QDL32070	QDA32070	QGL32070	QGA32070	QJL32070	QJA32070
80 A	1000 A	1800 A	QBL32080	QBA32080	QDL32080	QDA32080	QGL32080	QGA32080	QJL32080	QJA32080
90 A	1000 A	1800 A	QBL32090	QBA32090	QDL32090	QDA32090	QGL32090	QGA32090	QJL32090	QJA32090
100 A	1200 A	2400 A	QBL32100	QBA32100	QDL32100	QDA32100	QGL32100	QGA32100	QJL32100	QJA32100
110 A	1200 A	2400 A	QBL32110	QBA32110	QDL32110	QDA32110	QGL32110	QGA32110	QJL32110	QJA32110
125 A	1200 A	2400 A	QBL32125	QBA32125	QDL32125	QDA32125	QGL32125	QGA32125	QJL32125	QJA32125
150 A	1200 A	2400 A	QBL32150	QBA32150	QDL32150	QDA32150	QGL32150	QGA32150	QJL32150	QJA32150
175 A	1200 A	2400 A	QBL32175	QBA32175	QDL32175	QDA32175	QGL32175	QGA32175	QJL32175	QJA32175
200 A	1200 A	2400 A	QBL32200	QBA32200	QDL32200	QDA32200	QGL32200	QGA32200	QJL32200	QJA32200
225 A	1200 A	2400 A	QBL32225	QBA32225	QDL32225	QDA32225	QGL32225	QGA32225	QJL32225	QJA32225
250 A <sup>2</sup>	1200 A	2400 A	QBL32250	—	QDL32250	—	QGL32250	—	QJL32250	—

<sup>1</sup> 3P circuit breakers are rated 65 kA at 240/120 Vac, 3Ø, 4-wire delta or 100 kA at 208Y/120 Vac, 3Ø, 4-wire.

<sup>2</sup> 250 A is based on copper cable only.

<sup>3</sup> On 3P I-Line circuit breakers, add a 6 at the end of the catalog number to indicate CBA jaw configuration. Nothing added indicates a standard ABC jaw configuration.