

MULTI 9™ C60 Miniature Circuit Breakers

IEC 947-2 Rated MULTI 9™ C60 Miniature Circuit Breakers

MULTI 9 C60N Circuit Breaker — IEC 898: 6000A — IEC 947-2: 10 kA at 415 Vac



Rating (A)	1P	List Price	2P	List Price	3P	List Price	4P ^①	List Price
B Curve—Magnetic Setting Between 3 and 5 Ampere Rating								
1	24045	\$ 61	24071	\$ 131	24084	\$ 190	24097	\$ 251
2	24046	61	24072	131	24085	190	24098	251
3	24047	61	24073	131	24086	190	24099	251
4	24048	61	24074	131	24087	190	24100	251
6	24049	61	24075	131	24088	190	24101	251
10	24050	61	24076	131	24089	190	24102	251
16	24051	61	24077	131	24090	190	24103	251
20	24052	61	24078	131	24091	190	24104	251
25	24053	61	24079	131	24092	190	24105	251
32	20454	61	24080	131	24093	190	24106	251
40	24055	67	24081	135	24094	203	24107	254
50	24056	70	24082	144	24095	213	24108	264
63	24057	74	24083	152	24096	213	24109	272
C Curve—Magnetic Setting Between 5 and 10 Ampere Rating								
0.5	24067	74	24068	150	24069	218	24070	288
1	24395	61	24331	131	24344	190	24357	251
2	24396	61	24332	131	24345	190	24358	251
3	24397	61	24333	131	24346	190	24359	251
4	24398	61	24334	131	24347	190	24360	251
6	24399	61	24335	131	24348	190	24361	251
10	24401	61	24336	131	24349	190	24362	251
16	24403	61	24337	131	24350	190	24363	251
20	24404	61	24338	131	24351	190	24364	251
25	24405	61	24339	131	24352	190	24365	251
32	24406	61	24340	131	24353	190	24366	251
40	24407	67	24341	135	24354	203	24367	254
50	24408	70	24342	144	24355	213	24368	264
63	24409	74	24343	152	24356	213	24369	272
D Curve—Magnetic Setting Between 10 and 14 Ampere Rating								
1	24625	61	24653	131	24667	190	24681	251
2	24626	61	24654	131	24668	190	24682	251
3	24627	61	24655	131	24669	190	24683	251
4	24628	61	24656	131	24670	190	24684	251
6	24629	61	24657	131	24671	190	24685	251
10	24630	61	24658	131	24672	190	24686	251
16	24632	61	24660	131	24674	190	24688	251
20	24633	61	24661	131	24675	190	24689	251
25	24634	61	24662	131	24676	190	24690	251
32	24635	61	24663	131	24677	190	24691	251
40	24636	67	24664	135	24678	203	24692	254
50	24637	70	24665	144	24679	213	24693	264
63	24638	74	24666	152	24680	213	24694	272

① 4th Pole protected

Ratings and Interrupting ratings : page 12

Cable range : pressure terminals are suitable for solid copper cables:

■ 0.5 to 25A : 16mm² stranded or 25mm² solid

■ 32 to 63A : 25mm² stranded or 35mm² solid

Width in module of 9mm : 1P: (2) 9mm, 2P: (4) 9mm, 3P: (6) 9mm, 4P: (8) 9mm

Additional information:

■ Catalog no. 0860CT9501R10/98