

# Product data sheet

## Characteristics

# XB5AA841

red flush reset pushbutton Ø22 unmarked for 17...120 mm actuation distance

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 37.60 USD



### Main

Commercial Status	Commercialised
Range of product	Harmony XB5
Product or component type	Complete manual overload reset pushbutton
Device short name	XB5
Bezel material	Plastic
Fixing collar material	Plastic
Mounting diameter	0.87 in (22 mm)
Shape of signaling unit head	Round
Operator profile	Red flush unmarked
Activating distance	0.67...4.72 in (17...120 mm)

### Complementary

Height	1.14 in (29 mm)
Width	1.14 in (29 mm)
Depth	4.72 in (120 mm)
Product weight	0.06 lb(US) (0.027 kg)
Resistance to high pressure washer	1015.26 psi (7000000 Pa) at 131 °F (55 °C),distance: 0.1 m
Operating travel	0.39 in (10 mm)

### Environment

Protective treatment	TH
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Class of protection against electric shock	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 4X
IK degree of protection	IK03 conforming to IEC 50102
Standards	EN/IEC 60947-1
Product certifications	UL listed

### Ordering and shipping details

Category	22467 - PUSHBUTTONS,22MM(PLASTIC) NEW
Discount Schedule	CS2
GTIN	00785901383567
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	FR

Contractual warranty

---

Period	18 months
--------	-----------

---