

Product data sheet

Characteristics

QOB280VH

MINIATURE CIRCUIT BREAKER 240V 80A

Product availability: Stock - Normally stocked in distribution facility

Price*: 384.00 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	QO
[In] rated current	80 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Bolt-on
Poles description	2P
Short-circuit current	22 kA
Number of spaces required	2
Circuit breaker type	Standard
Circuit breaker application	Not rated
Electrical connection	Box lugs
AWG gauge	4...2/0 AWG aluminium 4...2/0 AWG copper
Accessory / separate part type	None

Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901120667
Nbr. of units in pkg.	1
Package weight(Lbs)	0.71
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------