

QO2701021

MINIATURE CIRCUIT BREAKER 120/240V 70A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 323.00 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	QO
[In] rated current	70 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	2P
Short-circuit current	10 kA
Number of spaces required	2
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Electrical connection	Box lugs
AWG gauge	8...2 AWG aluminium 8...2 AWG copper
Accessory / separate part type	Shunt trip 120/208/240 V AC

Ordering and shipping details

Category	00104 - QO 35-70A 1P;70-125A 2P CB
Discount Schedule	DE2A
GTIN	00785901494041
Nbr. of units in pkg.	1
Package weight(Lbs)	0.95
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------