

Product data sheet

Characteristics

QO120L100

LOADCTR QO MLO 240V 100A 1PH 20SP N1 SPL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 221.00 USD

Main

Commercial Status	Commercialised
Product or component type	Load Center
Range of product	QO
Load center type	Convertible Mains (lugs)
[In] rated current	100 A
Number of spaces	20
Short-circuit current	65 kA
Number of circuits	20
Number of tandem circuit breakers	0
Network number of phases	1 phase
[Ue] rated operational voltage	120/240 V AC

Complementary

NEMA degree of protection	NEMA 1 indoor
Cover type	Order separately
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Product certifications	UL listed

Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901577485
Nbr. of units in pkg.	1
Package weight(Lbs)	10.00
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	US

Contractual warranty

Period	18 months
--------	-----------