

# Product data sheet

## Characteristics

# PGA36080U44A

## MOLDED CASE CIRCUIT BREAKER 600V 800A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 19607.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Molded Case Circuit Breaker
Range of product	PowerPact P
Current sensor rating range	800 A
Product certifications	CSA IEC UL listed
[Ue] rated operational voltage	600 V AC
Mounting mode	Plug-in
Poles description	3P
Breaking capacity	18 kA 600 V AC 35 kA 480 V AC 65 kA 240 V AC
[Ics] rated service short-circuit breaking capacity	80 %
Electrical connection	Lugs load I-Line connection line
AWG gauge	3/0...500 AWG/kcmil aluminium/copper
Trip unit technology	Electronic ammeter Micrologic 6.0 A LSIG

### Ordering and shipping details

Category	01210 - PG,H,J,K,L,N I-LINE BREAKERS
Discount Schedule	DE2
GTIN	00785901458081
Nbr. of units in pkg.	1
Package weight(Lbs)	32.00
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	US

### Contractual warranty

Period	18 months
--------	-----------