

# Product data sheet

## Characteristics

# QO14252L200G

## LD CTR QO MOL 240V 200A 1PH 42SP NEMA 1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 810.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Load Center
Range of product	QO
Load center type	Convertible Mains (lugs)
[In] rated current	200 A
Number of spaces	42
Short-circuit current	65 kA
Number of circuits	52
Number of tandem circuit breakers	10
Network number of phases	1 phase
[Ue] rated operational voltage	120/240 V AC

### Complementary

AWG gauge	6...250 AWG/kcmil aluminium/copper
NEMA degree of protection	NEMA 1 indoor
Cover type	Order separately
Device composition	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Product certifications	UL listed

### Ordering and shipping details

Category	00001 - QO 1PH LC, 12-42 CKT, NEMA1
Discount Schedule	DE3A
GTIN	00785901574613
Nbr. of units in pkg.	1
Package weight(Lbs)	21.00
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

### Contractual warranty

Period	18 months
--------	-----------