

Product data sheet

Characteristics

QO14252L200GRB

LD CTR QO MLO 240V 200A 1PH 42SP NEMA
3R

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1194.00 USD

Main

Commercial Status	Commercialised
Product or component type	Load Center
Range of product	QO
Load center type	Convertible Mains (lugs)
[In] rated current	200 A
Number of spaces	42
Short-circuit current	65 kA
Number of circuits	52
Number of tandem circuit breakers	10
Network number of phases	1 phase
[Ue] rated operational voltage	120/240 V AC

Complementary

AWG gauge	6...250 AWG/kcmil aluminium/copper
NEMA degree of protection	NEMA 3R outdoor
Cover type	Surface cover
Device composition	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Product certifications	UL listed

Ordering and shipping details

Category	00002 - QO 1PH LC, 12-42 CKT, NEMA3R
Discount Schedule	DE3A
GTIN	00785901687313
Nbr. of units in pkg.	1
Package weight(Lbs)	39.00
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N

Contractual warranty

Period	18 months
--------	-----------