

Product data sheet

Characteristics

63T145HDIT

TRANSFORMER DRY 3PH 63KVA

460V-460Y/265V

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 10694.00 USD

Main

Commercial Status	Commercialised
Product or component type	Drive Isolation Transformer
Box number	20D
NEMA degree of protection	NEMA 2
Insulation temperature	428 °F (220 °C)
Network number of phases	3 phases
Primary voltage	460 V delta
Rated power in VA	63 kVA
Secondary voltage	460Y/265 V
Number of tap-offs	2 5 % 1+ 1-
Temperature rise	150 °C
Material	Aluminium

Ordering and shipping details

Category	16266 - DRIVE ISOLATION TRANSFORMERS
Discount Schedule	PE2
GTIN	00785901786030
Nbr. of units in pkg.	1
Package weight(Lbs)	520.00
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative