

# Product data sheet

## Characteristics

# 9070T2000D37

## TRANSFORMER CONTROL 2000VA

### 600V-120/240V

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1394.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Industrial Control Transformer
Product certifications	CE CSA UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	356 °F (180 °C)
Network number of phases	1 phase
Rated power in VA	2000 VA
Primary voltage	600 V 575 V
Secondary voltage	120/240 V 115/230 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Range of product	T

### Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901803638
Nbr. of units in pkg.	1
Package weight(Lbs)	48.60
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

### Contractual warranty

Period	10 years
--------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative