

Product data sheet

Characteristics

TSXCANCB50

CANopen cable - IP20 - UL - IEC 60332-2 - 50 m

Product availability: Stock - Normally stocked in distribution facility

Price*: 149.00 USD



Main

Commercial Status	Commercialised
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part designation	CANopen pre-formed cable
Accessory / separate part destination	CANopen bus
Cable length	164.04 ft (50 m)

Complementary

Marking	CE
Product weight	7.89 lb(US) (3.58 kg)

Environment

Product certifications	UL
IP degree of protection	IP20

Ordering and shipping details

Category	22558 - TSX PREMIUM, ATRIUM & PL7 PRO
Discount Schedule	PC22
GTIN	00785901748458
Nbr. of units in pkg.	1
Package weight(Lbs)	8.82
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	IT

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------