

# Product data sheet

## Characteristics

# 2510MBA1

## MANUAL STARTER 230VAC

Product availability: Stock - Normally stocked in distribution facility

Price\*: 363.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Manual Starter
Range of product	M
Product certifications	CSA UL listed
Auxiliary contact composition	Without
NEMA degree of protection	NEMA 12 painted sheet steel
Local signalling	No indicator
Motor power hp	2 hp 230 V AC 1 phase 1 hp 115 V AC 1 phase
[Ue] rated operational voltage	600 V AC
NEMA size	M-0
Poles description	2P
Control type	Pushbutton
Motor starter type	Non reversing
Electrical connection	Pressure wire clamp
Thermal overload type	Melting alloy
Number of thermal units required	1

### Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	00785901829713
Nbr. of units in pkg.	1
Package weight(Lbs)	6.97
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------