

# Product data sheet

## Characteristics

# 2510FG71P

## MANUAL STARTER 277VAC

Product availability: Stock - Normally stocked in distribution facility

Price\*: 264.00 USD



### Main

Commercial Status	Commercialised
Product or component type	Duplex Unit Manual Starter
Range of product	F
[In] rated current	16 A
Product certifications	CE CSA UL listed
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
NEMA degree of protection	NEMA 1 plastic standard size
Motor power hp	1 hp 277 V AC 1 hp 230 V AC 1 hp 115 V AC
[Ue] rated operational voltage	277 V AC
Poles description	1P
Control type	Toggle switch
Network number of phases	1 phase
Local signalling	Red indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
Thermal overload type	Melting alloy

### Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901554899
Nbr. of units in pkg.	1
Package weight(Lbs)	1.76
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------