

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 549.00 USD

NATO products



Main

Commercial Status	Commercialised
Range of product	9050A/H
Product or component type	Timer
[In] rated current	10 A
Switch function	DPDT
Contact operation	Time delayed 2 NO + 2 NC
Control circuit voltage	440 V AC 50 Hz 480 V AC 60 Hz
Ambient air temperature for operation	68...104 °F
Maximum switching voltage	600 V AC
Mounting support	Panel
Electrical connection	Screw-clamp terminals
Product certifications	CSA UL listed
Time delay type	On-delay
Time delay range	0.1 s...1 min
Reset response time	27 ms off-delay 29 ms on-delay

Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
GTIN	00785901866725
Nbr. of units in pkg.	1
Package weight(Lbs)	1.66
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------