

# QO125VH

## MINIATURE CIRCUIT BREAKER 120/240V 25A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 73.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	QO
[In] rated current	25 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	1P
Short-circuit current	22 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	Not rated
Electrical connection	Pressure plate
AWG gauge	14...8 AWG aluminium 14...8 AWG copper
Accessory / separate part type	None

### Ordering and shipping details

Category	00926 - QO IND SPECIALTY CB
Discount Schedule	DE2A
GTIN	00785901371793
Nbr. of units in pkg.	1
Package weight(Lbs)	0.54
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------