

# HJA260204

## Molded Case Circuit Breaker

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1589.00 USD

### Main

|                                |   |
|--------------------------------|---|
| Commercial Status              | Commercialised                                      |
| Product or component type      | Molded Case Circuit Breaker                         |
| Range of product               | PowerPact H   |
| [In] rated current             | 20 A  |
| Poles description              | 2P  |
| Breaking capacity              | 25 kA 600 V AC<br>65 kA 480 V AC<br>100 kA 240 V AC |
| [Ue] rated operational voltage | 600 V AC  |
| Trip unit technology           | Thermal-magnetic                                    |
| Product certifications         | CSA<br>IEC<br>UL listed                             |
| Mounting mode                  | Plug-in   |
| Breaking capacity code         | J   |
| Electrical connection          | Lugs load<br>I-Line connection line                 |
| AWG gauge                      | 14...3/0 AWG aluminium/copper                       |
| Phase connection               | BC  |
| Magnetic hold current          | 350 A   |
| Magnetic tripping current      | 750 A   |

### Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 01117 - HG, HJ, JG, JJ I-LINE BREAKER/SWITC               |
| Discount Schedule     | DE2   |
| GTIN                  | 00785901939122  |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 4.00  |
| Product availability  | Non-Stock - Not normally stocked in distribution facility |
| Returnability         | Y   |
| Country of origin     | US  |

### Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|