

Product data sheet

Characteristics

QO2175VH

MINIATURE CIRCUIT BREAKER 120/240V 175A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1061.00 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	QO
[In] rated current	175 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	2P
Short-circuit current	22 kA
Number of spaces required	4
Circuit breaker type	Standard
Circuit breaker application	Not rated
Electrical connection	Box lugs
AWG gauge	1...300 AWG/kcmil aluminium 1...300 AWG/kcmil copper
Accessory / separate part type	None

Ordering and shipping details

Category	00083 - QO BREAKERS 150-200 VH
Discount Schedule	DE2A
GTIN	00785901501299
Nbr. of units in pkg.	1
Package weight(Lbs)	2.50
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------