

Product data sheet

Characteristics

HLL36070

Molded Case Circuit Breaker

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3149.00 USD

Main

Commercial Status	Commercialised
Product or component type	Molded Case Circuit Breaker
Range of product	PowerPact H
[In] rated current	70 A
Poles description	3P
Breaking capacity	50 kA 600 V AC 100 kA 480 V AC 125 kA 240 V AC 20 kA 250 V DC
[Ue] rated operational voltage	250 V DC 600 V AC
[Ics] rated service short-circuit breaking capacity	80 %
Trip unit technology	Thermal-magnetic
Product certifications	CSA IEC UL listed
Mounting mode	Unit mount
Breaking capacity code	L
Electrical connection	Lugs line Lugs load
AWG gauge	14...3/0 AWG aluminium/copper
Magnetic hold current	800 A
Magnetic tripping current	1450 A

Ordering and shipping details

Category	01120 - HL,JL UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901883821
Nbr. of units in pkg.	1
Package weight(Lbs)	4.17
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	US

Contractual warranty

Period	18 months
--------	-----------