

Product data sheet

Characteristics

H228NR

SW,FUSIBLE 240V 1200A 2P NEMA3R NEUTRAL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 16665.00 USD

Main

Commercial Status	Commercialised
Product or component type	Single Throw Safety Switch
[In] rated current	1200 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3R galvanized steel
Device composition	Neutral (factory installed)
Disconnecter device type	Fusible disconnect
Short-circuit current	200 kA maximum L
Device mounting	Surface
Number of poles	2
Electrical connection	Lugs
Series name	Heavy duty
[Ue] rated operational voltage	240 V AC 250 V DC
AWG gauge	3/0...750 AWG/kcmil copper or aluminium

Ordering and shipping details

Category	00054 - H&HU SW,NEMA3R,400-1200A
Discount Schedule	DE1
GTIN	00785901259275
Nbr. of units in pkg.	1
Package weight(Lbs)	366.00
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	US

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative