

# Product data sheet

## Characteristics

# EE112T3HFCU

## Transformer Dry Type 112.5kVA 480D208Y

Product availability: Stock - Normally stocked in distribution facility

Price\*: 31706.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Energy Efficient Transformer
Box number	21D
NEMA degree of protection	NEMA 2
Insulation temperature	428 °F (220 °C)
Network number of phases	3 phases
Primary voltage	480 V delta
Rated power in VA	112.5 kVA
Secondary voltage	208Y/120 V
Number of tap-offs	6 2.5 % 2+ 4-
Temperature rise	115 °C
Material	Copper

### Ordering and shipping details

Category	16283 - 3 PH EE WATCHDOG LVGP XFMR
Discount Schedule	PE2E
GTIN	00785901709497
Nbr. of units in pkg.	1
Package weight(Lbs)	756.00
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative