

Product data sheet

Characteristics

QO340L200G

LOADCTR QO MLO 240V 200A 3PH 40SP-SP

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 818.00 USD

Main

Commercial Status	Commercialised
Product or component type	Load Center
Range of product	QO
Load center type	Fixed Mains (lugs)
[In] rated current	200 A
Number of spaces	40
Short-circuit current	65 kA
Number of circuits	40
Number of tandem circuit breakers	0
Network number of phases	3 phases
[Ue] rated operational voltage	240 V delta AC 240/120 V delta AC 208Y/120 V AC

Complementary

AWG gauge	6...300 AWG/kcmil aluminium/copper
NEMA degree of protection	NEMA 1 indoor
Cover type	Order separately
Device composition	Grounding bar included (not installed)
Electrical connection	Lugs
Wiring configuration	3-wire 4-wire
Material	Tin plated copper busbar
Product certifications	UL listed

Ordering and shipping details

Category	00011 - QO 3PH LOAD CENTER,INDOOR
Discount Schedule	DE3
GTIN	00785901310945
Nbr. of units in pkg.	1
Package weight(Lbs)	4.00
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N

Contractual warranty

Period	18 months
--------	-----------