

# Product data sheet

## Characteristics

# 8910DPA42V14

## Definite Purpose Contactor Type DPA 40A, 2-Pole, 24VAC@50/60Hz

Product availability: Stock - Normally stocked in distribution facility

Price\*: 79.00 USD



### Main

Commercial Status	Commercialised
Product or component type	Definite Purpose Contactor
[In] rated current	40 A
Motor power hp	7.5 hp 230 V AC 1 phase 3 hp 115 V AC 1 phase
Poles description	2P
Pole contact composition	2 NO
Control circuit voltage	24 V AC 50/60 Hz

### Complementary

Product certifications	CE CSA UL listed
Locked rotor rated current	160 A 575 V AC 200 A 460 V AC 240 A 277 V AC
[Ue] rated operational voltage	600 V AC
Network number of phases	1 phase
Electrical connection	Quick connect terminals
Range of product	DPA

### Ordering and shipping details

Category	21344 - 8910 DPA 4_(40 AMP)
Discount Schedule	CP1B
GTIN	00785901073482
Nbr. of units in pkg.	1
Package weight(Lbs)	1.10
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------