

HOM115HM

MINIATURE CIRCUIT BREAKER 120/240V 15A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 27.60 USD

Main

Commercial Status	Commercialised
Product or component type	Miniature Circuit Breaker
Range of product	Homeline
[In] rated current	15 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	High magnetic
Circuit breaker application	HACR rated
Electrical connection	Screw clamp terminals
AWG gauge	14...8 AWG aluminium/copper

Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901311195
Nbr. of units in pkg.	1
Package weight(Lbs)	0.32
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Contractual warranty

Period	Lifetime
--------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative