

8539SDA53V02S

STARTER MOTOR CONTROL <1000VAC

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3153.00 USD

Main

Commercial Status	Commercialised
Product or component type	Combination Starter
Range of product	S
Control circuit	Separate control circuit
Control type	No control units
NEMA degree of protection	NEMA 12 painted sheet steel with external reset
Auxiliary contact composition	Without
Motor power hp	20...25 hp 460 V AC 3 phases 7.5...10 hp 200 V AC 3 phases 25 hp 575 V AC 3 phases 10 hp 230 V AC 3 phases
Poles description	3P
[Ue] rated operational voltage	600 V AC
NEMA size	2
Control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Local signalling	No indicator
Motor starter type	Non reversing
Thermal overload type	Melting alloy
Number of thermal units required	3
Disconnecter device type	Mag-Gard circuit breaker

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901519782
Nbr. of units in pkg.	1
Package weight(Lbs)	42.94
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	MX

Contractual warranty

Period	18 months
--------	-----------