

HGA36025

Molded Case Circuit Breaker

Product availability: Stock - Normally stocked in distribution facility

Price*: 1575.00 USD

Main

Commercial Status	Commercialised
Product or component type	Molded Case Circuit Breaker
Range of product	PowerPact H
[In] rated current	25 A
Poles description	3P
Breaking capacity	18 kA 600 V AC 35 kA 480 V AC 65 kA 240 V AC
[Ue] rated operational voltage	600 V AC
Trip unit technology	Thermal-magnetic
Product certifications	CSA IEC UL listed
Mounting mode	Plug-in
Breaking capacity code	G
Electrical connection	Lugs load I-Line connection line
AWG gauge	14...3/0 AWG aluminium/copper
Phase connection	ABC
Magnetic hold current	350 A
Magnetic tripping current	750 A

Ordering and shipping details

Category	01117 - HG, HJ, JG, JJ I-LINE BREAKER/SWITC
Discount Schedule	DE2
GTIN	00785901700562
Nbr. of units in pkg.	1
Package weight(Lbs)	5.52
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Contractual warranty

Period	18 months
--------	-----------