

# Product data sheet

## Characteristics

# NSYTBP241910H

## PC box IP66 IK08 RAL7035 Int.H225W175D100 Ext.H241W194D105 opaque PC cover H20

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 58.60 USD



### Main

Commercial Status	Commercialised
Range of product	Thalassa TBP
Device application	Multi-purpose
Product or component type	Industrial box
Height	9.49 in (241 mm)
Width	7.64 in (194 mm)
Depth	4.21 in (107 mm)
Internal height	8.86 in (225 mm)
Internal width	6.89 in (175 mm)
Internal depth	3.94 in (100 mm)
Enclosure mounting	Wall mounted
Device composition	4 x cover screw 1 x cover 1 x body
Body type	One piece moulded
Type of front cover	High plain cover
Cover fixing	Plastic screws
Lock type	Outside sealed area: flat screwdriver captive screw
Removable parts	Cover, by captive screws

### Complementary

Material	Polycarbonate
Colour	Grey ( RAL 7035 )
Standards	IEC 62208 UL 508 A
Product certifications	DEMKO SEMKO TÜV UL
IP degree of protection	IP66conforming to NEMA 4.4X
IK degree of protection	IK08conforming to IEC 62262
Fire resistance	1760 °F (960 °C)
Ambient air temperature for storage	5...140 °F (-15...60 °C)
Ambient air temperature for operation	-13...176 °F (-25...80 °C)

### Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	00785901899549
Nbr. of units in pkg.	1
Package weight(Lbs)	2.20
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	HU

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0940 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------