

Square D General Purpose Relays

Class 8501R plug-in relays



8501RS41P14V20



8501RSD42P14V51



8501RS43P14V20



8501RS44P14V20

References					
Control circuit voltage	Number and type of contacts - Thermal current (Ith)				
	1 C/O - 15 A		2 C/O - 15 A		
	Unit reference	Weight kg/lb	Unit reference	Weight kg/lb	
Plug-in relays with standard cover (sold in lots of 1)					
12 Vdc	8501RSD41V51	0.026/0.057	8501RSD42V51	0.036/0.079	
24 Vdc	8501RSD41V53	0.026/0.057	8501RSD42V53	0.036/0.079	
110 Vdc	8501RSD41V60	0.026/0.057	8501RSD42V60	0.036/0.079	
12 Vac	8501RS41V36	0.026/0.057	8501RS42V36	0.036/0.079	
24 Vac	8501RS41V14	0.026/0.057	8501RS42V14	0.036/0.079	
120 Vac	8501RS41V20	0.026/0.057	8501RS42V20	0.036/0.079	
240 Vac	8501RS41V24	0.026/0.057	8501RS42V24	0.036/0.079	
Plug-in relays with standard cover and LED (sold in lots of 1)					
12 Vdc	8501RSD41P14V51	0.026/0.057	8501RSD42P14V51	0.036/0.079	
24 Vdc	8501RSD41P14V53	0.026/0.057	8501RSD42P14V53	0.036/0.079	
110 Vdc	8501RSD41P14V60	0.026/0.057	8501RSD42P14V60	0.036/0.079	
12 Vac	8501RS41P14V36	0.026/0.057	8501RS42P14V36	0.036/0.079	
24 Vac	8501RS41P14V14	0.026/0.057	8501RS42P14V14	0.036/0.079	
120 Vac	8501RS41P14V20	0.026/0.057	8501RS42P14V20	0.036/0.079	
240 Vac	8501RS41P14V24	0.026/0.057	8501RS42P14V24	0.036/0.079	
Control circuit voltage	Number and type of contacts - Thermal current (Ith)				
	3 C/O - 15 A		4 C/O - 15 A		
	Unit reference	Weight kg/lb	Unit reference	Weight kg/lb	
Plug-in relays with standard cover (sold in lots of 1)					
12 Vdc	8501RSD43V51	0.054/0.119	8501RSD44V51	0.071/0.157	
24 Vdc	8501RSD43V53	0.054/0.119	8501RSD44V53	0.071/0.157	
110 Vdc	8501RSD43V60	0.054/0.119	8501RSD44V60	0.071/0.157	
12 Vac	8501RS43V36	0.054/0.119	8501RS44V36	0.071/0.157	
24 Vac	8501RS43V14	0.054/0.119	8501RS44V14	0.071/0.157	
120 Vac	8501RS43V20	0.054/0.119	8501RS44V20	0.071/0.157	
240 Vac	8501RS43V24	0.054/0.119	8501RS44V24	0.071/0.157	
Plug-in relays with standard cover and LED (sold in lots of 1)					
12 Vdc	8501RSD43P14V51	0.054/0.119	8501RSD44P14V51	0.071/0.157	
24 Vdc	8501RSD43P14V53	0.054/0.119	8501RSD44P14V53	0.071/0.157	
110 Vdc	8501RSD43P14V60	0.054/0.119	8501RSD44P14V60	0.071/0.157	
12 Vac	8501RS43P14V36	0.054/0.119	8501RS44P14V36	0.071/0.157	
24 Vac	8501RS43P14V14	0.054/0.119	8501RS44P14V14	0.071/0.157	
120 Vac	8501RS43P14V20	0.054/0.119	8501RS44P14V20	0.071/0.157	
240 Vac	8501RS43P14V24	0.054/0.119	8501RS44P14V24	0.071/0.157	