

8538SBG13V02S

Combination Starter , Non-Reversing, NEMA Size: 0, 3-Phase, 3-Pole



List Price \$896.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Control Source	Separate Control Circuit
Overload Type	Thermal - Melting Alloy
Phase	3-Phase
Catalog Reference Number	8538CT9701
Disconnect Type	Fusible Disconnect Switch
Enclosure Type	General Purpose (Indoor)
Enclosure Rating	NEMA 1
Fuse Clip Amperes	30A
Fuse Type	Class H
Horsepower Rating (3-Phase)	5HP@460/575VAC
NEMA Size	0
Maximum Voltage Rating	600VAC
Mounting Type	Surface
Number of Poles	3-Pole
Operating Voltage	120VAC@60Hz - 110VAC@50Hz
Width	9.50 Inches
Height	22.50 Inches
External Reset	Yes
Action	Non-Reversing
Thermal Units Required	3
Depth	8.34 Inches
Type	S
Weight	38 Pounds

Shipping and Ordering

Category	21212 - Starters, Combination, NEMA, Enclosed (NEMA 1 & 12), Size 0
Discount Schedule	CP1
Article Number	785901748243
Package Quantity	1
Weight	34.89 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y

Generated: 06/16/2009 04:34:06