

List Price \$89.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Ampere Rating	10A
Approvals	UL File Number E42259 CCN NKCR - CSA File Number LR24590 Class 3211-03 - CE Marked
Bezel Material	Chromium Plated Metal
Button/Cap Color	Universal (Contains 1 of each: Black, Red, Green, Yellow, Orange, Blue and White)
Button Type	Standard Pushbutton
Guard Type	Extended Guard (Metal)
Contact Configuration	1 NO - 1 NC
Contact Block Code	H13
Contact Type	Standard (Fingersafe)
Enclosure Type	Water tight, Dust tight and Oil tight (Indoor/Outdoor)
Enclosure Rating	NEMA 1/2/3/3R/4/6/12/13
Head Type	Round
Light Module Supply Voltage	n/a
Light Module Type	n/a
Markings	None
Maximum Voltage Rating	600V
Mounting Type	Panel
Number of Operators	1
Number of Positions	2
Operator Action	Momentary
Operator Type	Non-Illuminated
Size	30mm
Terminal Type	Screw Clamp
Type	K
Utilization Category	AC15 - DC13

**Shipping and Ordering**

Category	21426 - Push Buttons, 30 mm, Metal, Round, Type K
Discount Schedule	CS1
GTIN	00785901856870
Package Quantity	1
Weight	0.31 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 10/06/2016 16:14:30