

Main

Approvals	UL Listed File Number E42259 CCN NKCR - CSA Certified File Number LR25490 Class 3211 03 - CE Marked
Bezel Material	Plastic
Enclosure Rating	NEMA 4/4X/13
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Head Type	Round
Lens Type	No Lens
Light Module Supply Voltage	208/220VAC@50/60Hz
Light Module Type	Transformer
Mounting Position	All
Mounting Type	Panel
Operator Type	Standard
Size	30mm
Terminal Type	Screw Clamp
Type	SK

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.